

**SAK Series
STB 18/RSF1**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image

Similar to illustration

Klippon® Connect with clamping yoke Technology

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	STB 18/RSF1
Order No.	0286500000
Version	SAK Series, Socket
GTIN (EAN)	4008190515591
Qty.	20 pc(s).

SAK Series
STB 18/RSF1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Depth	23 mm	Depth (inches)	0.906 inch
Net weight	2.9 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C		

Material data

Colour	beige
--------	-------

System specifications

Version	For the mounting rails
---------	------------------------

Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

Dimensions

Plug-in depth	15 mm
---------------	-------

Classifications

ETIM 3.0	EC001134	ETIM 4.0	EC001134
ETIM 5.0	EC001134	ETIM 6.0	EC002848
UNSPSC	30-21-18-11	eClass 5.1	27-14-11-45
eClass 6.2	27-14-92-14	eClass 7.1	27-14-92-14
eClass 8.1	27-14-92-14	eClass 9.0	27-14-11-92
eClass 9.1	27-14-11-92		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Engineering Data	STEP
------------------	----------------------