

**SAK Series  
QL 4 DLI**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Product image**

Similar to illustration

**Signal wiring**

Tailored and particularly compact: with our AIO initiator/actuator terminal blocks, you are relying on an application-optimised solution for signal wiring. We also offer you other terminal blocks featuring spring and screw connection technology for signal wiring.

**General ordering data**

Type	QL 4 DLI
Order No.	<a href="#">0297400000</a>
Version	SAK Series, Cross-connection lug, for screwable cross-connection, No. of poles: 4
GTIN (EAN)	4008190165482
Qty.	50 pc(s).

## Data sheet

### SAK Series QL 4 DLI

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Width	23.3 mm	Width (inches)	0.917 inch
Height	4 mm	Height (inches)	0.157 inch
Depth	0.8 mm	Depth (inches)	0.031 inch
Net weight	0.44 g		

### Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C		

### Material data

Material	Copper	Surface finish	tinned
Colour	grey		

### System specifications

Version	for screwable cross-connection
---------	--------------------------------

### Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

### Dimensions

Pitch in mm (P)	6.1 mm
-----------------	--------

### Classifications

ETIM 3.0	EC000489	ETIM 4.0	EC000489
ETIM 5.0	EC000489	ETIM 6.0	EC000489
UNSPSC	30-21-18-01	eClass 5.1	27-14-11-40
eClass 6.2	27-14-11-40	eClass 7.1	27-14-11-40
eClass 8.1	27-14-11-40	eClass 9.0	27-14-11-40
eClass 9.1	27-14-11-40		

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">STEP</a>
------------------	----------------------