

SAK Series, Accessories
QVS 2 SAKT1+2**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

The versatile and extensive range of products - from 0.05 mm² to 300 mm² - means that you have diverse options for your applications at your disposal.
Hardened steel for mechanical strength and high-quality tinned copper for optimum conductivity. All materials comply with RoHS requirements and have been tested to current environment guidelines.

General ordering data

Type	QVS 2 SAKT1+2
Order No.	0307300000
Version	SAK Series, Accessories, Cross-connector, Cross-connector, No. of poles: 2
GTIN (EAN)	4008190036140
Qty.	20 pc(s).

SAK Series, Accessories QVS 2 SAKT1+2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	23.7 mm	Width	15.4 mm
Height	2.5 mm	Net weight	0.95 g

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Version	Cross-connector		

Material data

Material	PA 66	Colour	Beige
UL 94 flammability rating	V-2		

System specifications

Product family	SAK Series, Accessories
----------------	-------------------------

Classifications

ETIM 3.0	EC000489	UNSPSC	30-21-18-01
eClass 5.1	27-14-11-40	eClass 6.2	27-14-11-40
eClass 7.1	27-14-11-40		

Approvals

ROHS	Conform
------	---------