


SAK Series, Accessories
QVS 4 SAKT1+2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**QVS4 030740**

The versatile and extensive range of products - from 0.05 mm² to 300 mm² - means that you have diverse options for your applications at your disposal.
Hardened steel for mechanical strength and high-quality tinned copper for optimum conductivity. All materials comply with RoHS requirements and have been tested to current environment guidelines.

General ordering data

Type	QVS 4 SAKT1+2
Order No.	0307400000
Version	SAK Series, Accessories, Cross-connector, Cross-connector, No. of poles:
GTIN (EAN)	4008190091941
Qty.	20 pc(s).

SAK Series, Accessories QVS 4 SAKT1+2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	22 mm	Width	30 mm
Height	4.5 mm	Net weight	2.2 g

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Additional technical data

Version	Cross-connector
---------	-----------------

Material data

Material	PA 66	Colour	Beige
UL 94 flammability rating	V-2		

System specifications

Product family	SAK Series, Accessories
----------------	-------------------------

Classifications

ETIM 3.0	EC000489	UNSPSC	30-21-18-01
eClass 5.1	27-14-11-40	eClass 6.2	27-14-11-40
eClass 7.1	27-14-11-40		

Approvals

ROHS	Conform
------	---------