

**SAK Series**  
**TW SAKD2.5N HP/TF/0.5****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com**Product image**

Similar to illustration

**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

Type	TW SAKD2.5N HP/TF/0.5
Order No.	<a href="#">0307500000</a>
Version	SAK Series, Separation plate, 0.5 mm, beige
GTIN (EAN)	4008190110017
Qty.	20 pc(s).

**SAK Series**  
**TW SAKD2.5N HP/TF/0.5**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Width	0.5 mm	Width (inches)	0.02 inch
Height	32.5 mm	Height (inches)	1.28 inch
Depth	46 mm	Depth (inches)	1.811 inch
Net weight	1.05 g		

**Temperatures**

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

**Material data**

Material	PA 66	Colour	beige
UL 94 flammability rating	V-2		

**System specifications**

Version	Intermediate plate
---------	--------------------

**Additional technical data**

Snap-on	No
---------	----

**Dimensions**

TS 32 offset	16.25 mm
--------------	----------

**Classifications**

ETIM 3.0	EC000886	ETIM 4.0	EC000886
ETIM 5.0	EC000886	ETIM 6.0	EC000886
UNSPSC	30-21-18-27	eClass 5.1	27-14-11-33
eClass 6.2	27-14-11-33	eClass 7.1	27-14-11-33
eClass 8.1	27-14-11-33	eClass 9.0	27-14-11-92
eClass 9.1	27-14-11-33		

**Approvals**

ROHS	Conform
------	---------