

SAK Series, Accessories
Q 2 AKZ1.5**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

This type of cross-connection has a pre-assembled captive cross-connection lug, cross-connection sleeve and fixing screw.

All the individual parts are available separately on request.

During installation, the pre-assembled cross-connectors are simply placed in the cross-connection slot in the middle of the terminal and screwed tight.

General ordering data

| | |
|------------|--|
| Type | Q 2 AKZ1.5 |
| Order No. | 0368200000 |
| Version | SAK Series, Accessories, Cross-connector, for cross-connection link, No. of poles: 2 |
| GTIN (EAN) | 4008190149987 |
| Qty. | 50 pc(s). |

SAK Series, Accessories Q 2 AKZ1.5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|--------|-------|------------|--------|
| Length | 4 mm | Width | 9.1 mm |
| Height | 11 mm | Net weight | 1.62 g |

Temperatures

| | |
|-----------------------|---------------------|
| Operating temperature | Storage temperature |
|-----------------------|---------------------|

Additional technical data

| | | | |
|--------------------------|---------------------------|---------------------|-----------------|
| Explosion-tested version | No | Installation advice | Direct mounting |
| Version | for cross-connection link | | |

Rated data

| | |
|---------------|------|
| Rated current | 24 A |
|---------------|------|

Material data

| | | | |
|----------|-------|--------|------|
| Material | Cu Zn | Colour | Grey |
|----------|-------|--------|------|

System specifications

| | |
|----------------|-------------------------|
| Product family | SAK Series, Accessories |
|----------------|-------------------------|

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000489 | UNSPSC | 30-21-18-01 |
| eClass 5.1 | 27-14-11-40 | eClass 6.2 | 27-14-11-40 |
| eClass 7.1 | 27-14-11-40 | | |

Product information

| | |
|---------------------------------|---|
| Descriptive text technical data | 24 A for max. conductor size of 2.5 mm ² |
|---------------------------------|---|

Approvals

| | |
|-----------|---------|
| Approvals | |
| ROHS | Conform |

Downloads

| | |
|------|---|
| DXF | 04444_Q_2_AKZ1.5_DXF.dxf |
| STEP | 0368200000_04444_Q_2_AKZ1.5_STP.stp |