

SAK Series, Accessories
Q 4 AKZ1.5**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

This type of cross-connection has a pre-assembled captive cross-connection lug, cross-connection sleeve and fixing screw.

All the individual parts are available separately on request. During installation, the pre-assembled cross-connectors are simply placed in the cross-connection slot in the middle of the terminal and screwed tight.

General ordering data

Type	Q 4 AKZ1.5
Order No.	0368400000
Version	SAK Series, Accessories, Cross-connector, for cross-connection link, No. of poles: 4
GTIN (EAN)	4008190153892
Qty.	50 pc(s).

SAK Series, Accessories Q 4 AKZ1.5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	4 mm	Width	19.3 mm
Net weight	3.36 g		

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Version	for cross-connection link		

Rated data

Rated current	24 A
---------------	------

Material data

Colour	Grey
--------	------

System specifications

Product family	SAK Series, Accessories
----------------	-------------------------

Classifications

ETIM 3.0	EC000489	UNSPSC	30-21-18-01
eClass 5.1	27-14-11-40	eClass 6.2	27-14-11-40
eClass 7.1	27-14-11-40		

Product information

Descriptive text technical data	24 A for max. conductor size of 2.5 mm ²
---------------------------------	---

Approvals

Approvals	
ROHS	Conform

Downloads

DXF	04444_Q_4_AKZ1.5_DXF.dxf
STEP	0368400000_04444_Q_4_AKZ1.5_STP.stp