

H2,5/7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

For conductors from 0.25 to 6,0 mm² (AWG 24 - 10)

tin-plated copper

dimensional tolerances to DIN 46228 part 1

- supplied loose in polybag

General ordering data

Type	H2,5/7
Order No.	0373000000
Version	Wire end ferrule, 2.5 mm ²
GTIN (EAN)	4008190173463
Qty.	1,000 pc(s).

H2,5/7

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	7 mm	Net weight	0.067 g
--------	------	------------	---------

Product data

Conductor cross-section	2.5 mm ²	Wire connection cross section AWG, max.	AWG 14
Contact surface diameter (D1)	2.2 mm	Collar diameter (D2)	3.4 mm

Classifications

ETIM 3.0	EC000005	UNSPSC	31-16-31-02
eClass 5.1	27-40-02-01	eClass 6.2	27-40-02-01
eClass 7.1	27-40-02-01		

Approvals

Approvals



ROHS	Conform
------	---------