

**W-Series
IH 2.8 DB**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	IH 2.8 DB
Order No.	0386060000
Version	W-Series, Insulating sleeve
GTIN (EAN)	4008190043414
Qty.	100 pc(s).

W-Series
IH 2.8 DB

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	3.6 mm	Width (inches)	0.142 inch
Height	18 mm	Height (inches)	0.709 inch
Depth	5.1 mm	Depth (inches)	0.201 inch
Net weight	0.19 g		

Temperatures

Operating temperature, min.	-50 °C	Storage temperature, max.	40 °C
Storage temperature, min.	10 °C	Operating temperature	-50 °C...
Storage temperature	10 °C...40 °C	Continuous operating temp., max.	120 °C

Material data

Material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
--------------------------	----	---------------------	-----------------

UL rating data

Certificate No. (UR)	E60693
----------------------	--------

Classifications

ETIM 5.0	EC002848	ETIM 6.0	EC002848
UNSPSC	30-21-18-11	eClass 5.1	27-14-11-45
eClass 6.2	27-14-92-14	eClass 7.1	27-14-92-14
eClass 8.1	27-14-92-14	eClass 9.0	27-14-11-92
eClass 9.1	27-14-11-92		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Engineering Data	STEP
------------------	----------------------