

**SAK Series**  
**AP DK4/380 Q****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com**Product image**

Similar to illustration

**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

Type	AP DK4/380 Q
Order No.	<a href="#">0438560000</a>
Version	SAK Series, End plate, 1.5 mm, beige, Direct mounting
GTIN (EAN)	4008190133351
Qty.	20 pc(s).

## Data sheet

### SAK Series AP DK4/380 Q

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Width	1.5 mm	Width (inches)	0.059 inch
Height	51 mm	Height (inches)	2.008 inch
Depth	41 mm	Depth (inches)	1.614 inch
Net weight	2.8 g		

### Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

### Material data

Material	PA 66	Colour	beige
UL 94 flammability rating	V-2		

### System specifications

Version	End plate
---------	-----------

### Additional technical data

Installation advice	Direct mounting	Snap-on	Yes
---------------------	-----------------	---------	-----

### Classifications

ETIM 3.0	EC000886	ETIM 4.0	EC000886
ETIM 5.0	EC000886	ETIM 6.0	EC000886
UNSPSC	30-21-18-27	eClass 5.1	27-14-11-33
eClass 6.2	27-14-11-33	eClass 7.1	27-14-11-33
eClass 8.1	27-14-11-33	eClass 9.1	27-14-11-33

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">EPLAN</a>
------------------	-----------------------