

**SAK Series  
VL 2 AKZ4/DK4**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Product image**

VL2 044670

**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

Type	VL 2 AKZ4/DK4
Order No.	<a href="#">0446700000</a>
Version	SAK Series, Cross-connection lug, for cross-connection link, No. of poles: 2
GTIN (EAN)	4008190055486
Qty.	50 pc(s).

**SAK Series  
VL 2 AKZ4/DK4**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Width	5 mm	Width (inches)	0.197 inch
Height	11 mm	Height (inches)	0.433 inch
Depth	1 mm	Depth (inches)	0.039 inch
Net weight	0.32 g		

**Temperatures**

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C		

**Material data**

Material	Cu Zn	Colour	grey
----------	-------	--------	------

**System specifications**

Version	for cross-connection link
---------	---------------------------

**Additional technical data**

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

**Dimensions**

Pitch in mm (P)	6 mm
-----------------	------

**Classifications**

ETIM 3.0	EC000489	ETIM 4.0	EC000489
ETIM 5.0	EC000489	ETIM 6.0	EC000489
UNSPSC	30-21-18-01	eClass 5.1	27-14-11-40
eClass 6.2	27-14-11-40	eClass 7.1	27-14-11-40
eClass 8.1	27-14-11-40	eClass 9.0	27-14-11-40
eClass 9.1	27-14-11-40		

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">STEP</a>
------------------	----------------------