

**SAK Series**  
**TW AST1/PA HP/DBR/0.5****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com**Product image****Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

Type	TW AST1/PA HP/DBR/0.5
Order No.	<a href="#">0474700000</a>
Version	SAK Series, Separation plate, 0.5 mm, dark brown
GTIN (EAN)	4008190078508
Qty.	20 pc(s).

## Data sheet

### SAK Series TW AST1/PA HP/DBR/0.5

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Width	0.5 mm	Width (inches)	0.02 inch
Height	65 mm	Height (inches)	2.559 inch
Depth	60 mm	Depth (inches)	2.362 inch
Net weight	2.5 g		

### Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

### Material data

Colour	dark brown	UL 94 flammability rating	V-2
--------	------------	---------------------------	-----

### System specifications

Version	Intermediate plate
---------	--------------------

### Additional technical data

Snap-on	Yes
---------	-----

### Dimensions

TS 32 offset	32.5 mm
--------------	---------

### Classifications

ETIM 3.0	EC000886	ETIM 4.0	EC000886
ETIM 5.0	EC000886	ETIM 6.0	EC000886
UNSPSC	30-21-18-27	eClass 5.1	27-14-11-33
eClass 6.2	27-14-11-33	eClass 7.1	27-14-11-33
eClass 8.1	27-14-11-33	eClass 9.0	27-14-11-92
eClass 9.1	27-14-11-33		

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">STEP</a>
------------------	----------------------