

**SAK Series, Accessories**  
**QB 2 WI RA6 IS****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

Cross-connection element, insulated  
6.0, 6.5 mm and 8.0 mm pitches

**General ordering data**

Type	QB 2 WI RA6 IS
Order No.	<a href="#">0482700000</a>
Version	SAK Series, Accessories, Cross-connector, for cross-connection link, No. of poles: 2
GTIN (EAN)	4008190166021
Qty.	50 pc(s).

**Datenblatt**

**SAK Series, Accessories  
QB 2 WI RA6 IS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technische Daten**

**Dimensions and weights**

Length	12 mm	Width	3 mm
Height	19 mm	Net weight	0.79 g

**Temperatures**

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

**Additional technical data**

Explosion-tested version	No	Installation advice	Direct mounting
Version	for cross-connection link		

**Material data**

Material	PA 66	Colour	Grey
UL 94 flammability rating	V-2		

**System specifications**

Product family	SAK Series, Accessories
----------------	-------------------------

**Classifications**

ETIM 3.0	EC000489	UNSPSC	30-21-18-01
eClass 5.1	27-14-11-40	eClass 6.2	27-14-11-40
eClass 7.1	27-14-11-40		

**Product information**

Descriptive text technical data	The mounting tolerances of the terminals must be taken into account. When used with a cross-connector, the rated cross-section should be reduced to the next smallest diameter.
---------------------------------	---

**Approvals**

Approvals	
ROHS	Conform