

SAK Series, Accessories
QB 3 WI RA6 IS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Cross-connection element, insulated
6.0, 6.5 mm and 8.0 mm pitches

General ordering data

Type	QB 3 WI RA6 IS
Order No.	0482800000
Version	SAK Series, Accessories, Cross-connector, for cross-connection link, No. of poles: 3
GTIN (EAN)	4008190145217
Qty.	50 pc(s).

SAK Series, Accessories QB 3 WI RA6 IS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	20 mm	Width	3 mm
Height	19 mm	Net weight	1.23 g

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Version	for cross-connection link		

Material data

Material	PA 66	Colour	Grey
UL 94 flammability rating	V-2		

System specifications

Product family	SAK Series, Accessories
----------------	-------------------------

Classifications

ETIM 3.0	EC000489	UNSPSC	30-21-18-01
eClass 5.1	27-14-11-40	eClass 6.2	27-14-11-40
eClass 7.1	27-14-11-40		

Product information

Descriptive text technical data	The mounting tolerances of the terminals must be taken into account. When used with a cross-connector, the rated cross-section should be reduced to the next smallest diameter.
---------------------------------	---

Approvals

Approvals



ROHS	Conform
------	---------