

**SAK Series, Accessories**  
**QB 4 WI RA6 IS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



Cross-connection element, insulated  
6.0, 6.5 mm and 8.0 mm pitches

**General ordering data**

|            |                                                                                      |
|------------|--------------------------------------------------------------------------------------|
| Type       | QB 4 WI RA6 IS                                                                       |
| Order No.  | <a href="#">0482900000</a>                                                           |
| Version    | SAK Series, Accessories, Cross-connector, for cross-connection link, No. of poles: 4 |
| GTIN (EAN) | 4008190086169                                                                        |
| Qty.       | 50 pc(s).                                                                            |

## SAK Series, Accessories QB 4 WI RA6 IS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Dimensions and weights

|        |       |            |        |
|--------|-------|------------|--------|
| Length | 28 mm | Width      | 3 mm   |
| Height | 19 mm | Net weight | 1.65 g |

### Temperatures

|                                  |        |                                  |        |
|----------------------------------|--------|----------------------------------|--------|
| Operating temperature            |        | Storage temperature              |        |
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 100 °C |

### Additional technical data

|                          |                           |                     |                 |
|--------------------------|---------------------------|---------------------|-----------------|
| Explosion-tested version | No                        | Installation advice | Direct mounting |
| Version                  | for cross-connection link |                     |                 |

### Material data

|                           |       |        |      |
|---------------------------|-------|--------|------|
| Material                  | PA 66 | Colour | Grey |
| UL 94 flammability rating | V-2   |        |      |

### System specifications

|                |                         |
|----------------|-------------------------|
| Product family | SAK Series, Accessories |
|----------------|-------------------------|

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000489    | UNSPSC     | 30-21-18-01 |
| eClass 5.1 | 27-14-11-40 | eClass 6.2 | 27-14-11-40 |
| eClass 7.1 | 27-14-11-40 |            |             |

### Product information

|                                 |                                                                                                                                                                                 |
|---------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Descriptive text technical data | The mounting tolerances of the terminals must be taken into account. When used with a cross-connector, the rated cross-section should be reduced to the next smallest diameter. |
|---------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

### Approvals

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|