

**Accessories
MOFU 35****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Weidmüller offers users of modular terminals a comprehensive range of accessories that render possible appropriate solutions for all - even non-standard - tasks.

General ordering data

Type	MOFU 35
Order No.	0495660000
Version	Accessories, Mounting foot, Polyamide 66
GTIN (EAN)	4008190048518
Qty.	20 pc(s).

Accessories
MOFU 35

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten**Dimensions and weights**

Length	58 mm	Width	18 mm
Height	18.35 mm	Net weight	5.935 g

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

Additional technical data

Explosion-tested version	No	Open sides	right
Type of mounting	Snap-on	Version	Mounting foot

Clampable wires (rated connection)

Type of connection	Tension clamp connection	Connection direction	top
--------------------	--------------------------	----------------------	-----

Material data

Insulating material	PA 66	Material	Polyamide 66
Colour	Orange	UL 94 flammability rating	V-2

System specifications

Product family	Accessories	Type of connection	Tension clamp connection
Connection direction	top	End cover plate required	No

Classifications

ETIM 3.0	EC000897	UNSPSC	30-21-18-11
eClass 5.1	27-14-11-45	eClass 6.2	27-14-92-14
eClass 7.1	27-14-92-14		

Approvals

Approvals



ROHS	Conform
------	---------