

**VPMS (blanking plug in brass)  
VP 42-MS65**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



For sealing surplus threaded holes to maintain the IP class of protection

**General ordering data**

Type	VP 42-MS65
Order No.	<a href="#">0501300000</a>
Version	VPMS (blanking plug in brass), Blanking plug, PG 42, 10 mm, Brass, nickel-plated
GTIN (EAN)	4008190007676
Qty.	25 pc(s).

**Data sheet**

**VPMS (blanking plug in brass)  
VP 42-MS65**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data**

**Dimensions and weights**

Length	16 mm	Length (inches)	0.63 inch
Height	16 mm	Height (inches)	0.63 inch
Net weight	45.48 g	Diameter	57 mm

**General information**

Cable glands	PG	External thread	PG 42
Head diameter	57 mm	Length of thread	10 mm
Material	Brass, nickel-plated	O-Ring	NBR
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Protection degree	IP68	Sealing	NBR

**Classifications**

ETIM 3.0	EC000032	ETIM 4.0	EC000032
ETIM 5.0	EC000032	ETIM 6.0	EC000451
UNSPSC	30-21-18-01	eClass 5.1	27-14-91-10
eClass 6.2	27-14-91-10	eClass 7.1	27-14-91-10
eClass 8.1	27-14-91-10	eClass 9.0	27-14-44-25
eClass 9.1	27-14-44-33		

**Approvals**

Approvals



ROHS Conform

**Downloads**

Brochure/Catalogue	<a href="#">CAT 3 HDC 17/18 EN</a> <a href="#">CAT 5 ENCL 17/18 EN</a>
Engineering Data	<a href="#">EPLAN.WSCAD</a>
Engineering Data	<a href="#">STEP</a>

**Data sheet**

**VPMS (blanking plug in brass)  
VP 42-MS65**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

