

SAK Series, Accessories
QB 58/8/15

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Poles are easy to break off for contacts that do not require a connection.

Cross-connection, plain-cut (with insulation profile as electric-shock protection if required).

6.0 mm and 8.0 mm pitches

The mounting tolerances of the terminals must be taken into account.

General ordering data

Type	QB 58/8/15
Order No.	0545400000
Version	SAK Series, Accessories, Cross-connector, for cross-connection link, No. of poles: 58
GTIN (EAN)	4008190028794
Qty.	10 pc(s).

SAK Series, Accessories

QB 58/8/15

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	458.5 mm	Width	0.8 mm
Height	17.5 mm	Net weight	21.96 g

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Version	for cross-connection link		

Material data

Material	Copper	Colour	Grey
----------	--------	--------	------

System specifications

Product family	SAK Series, Accessories
----------------	-------------------------

Classifications

ETIM 3.0	EC000489	UNSPSC	30-21-18-01
eClass 5.1	27-14-11-40	eClass 6.2	27-14-11-40
eClass 7.1	27-14-11-40		

Product information

Descriptive text technical data	The mounting tolerances of the terminals must be taken into account. When used with a cross-connector, the rated cross-section should be reduced to the next smallest diameter.
---------------------------------	---

Approvals

Approvals



ROHS	Conform
------	---------