

**Conductor markers  
CLI R 1-3 GE/SW 7**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



The Weidmüller range of conductor and cable marker products provides users with solutions for the most diverse applications. The range of applications extends from narrow conductors right up to cables with large outside diameters. Among the products in the range are combination systems with individual tags, transparent sleeves, shrink-fit sleeves and markers, which can be fixed with cable ties.

**General ordering data**

|            |                                                                                             |
|------------|---------------------------------------------------------------------------------------------|
| Type       | CLI R 1-3 GE/SW 7                                                                           |
| Order No.  | <a href="#">0572901524</a>                                                                  |
| Version    | Conductor markers, Mounting mandrel, 3 x 4.2 mm, PVC, soft, without Cadmium, Colour: Yellow |
| GTIN (EAN) | 4008190003470                                                                               |
| Qty.       | 10 pc(s).                                                                                   |

## Conductor markers CLI R 1-3 GE/SW 7

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |       |       |        |
|------------|-------|-------|--------|
| Length     | 3 mm  | Width | 4.2 mm |
| Height     | 5 mm  | Depth | 5 mm   |
| Net weight | 2.4 g |       |        |

### General data

|                                   |                            |                                              |            |
|-----------------------------------|----------------------------|----------------------------------------------|------------|
| Colour                            | Yellow                     | Colour of printing                           | Black      |
| Material                          | PVC, soft, without Cadmium | Material colour according to resistance code | 4          |
| Number per mandrel                | 25                         | Operating temperature range, max.            | 80 °C      |
| Operating temperature range, min. | 30 °C                      | Orientation of print                         | horizontal |
| Printed characters                | Numbers                    | Printing                                     | 7          |
| Printing method                   | Laser print                | Type of printing                             | Standard   |
| UL 94 flammability rating         | V-0                        |                                              |            |

### Conductor and cable markers

|                               |                   |                               |                     |
|-------------------------------|-------------------|-------------------------------|---------------------|
| Conductor O.D., max.          | 5 mm              | Conductor O.D., min.          | 3 mm                |
| Conductor cross-section, max. | 4 mm <sup>2</sup> | Conductor cross-section, min. | 1.5 mm <sup>2</sup> |
| Halogen                       | Yes               |                               |                     |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001530    | UNSPSC     | 44-12-17-08 |
| eClass 5.1 | 27-14-91-03 | eClass 6.2 | 27-14-91-29 |
| eClass 7.1 | 27-14-91-29 |            |             |

### Approvals

|           |         |
|-----------|---------|
| Approvals |         |
| ROHS      | Conform |