

**Conductor markers
CLI R 1-3 GE/SW 9**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The Weidmüller range of conductor and cable marker products provides users with solutions for the most diverse applications. The range of applications extends from narrow conductors right up to cables with large outside diameters. Among the products in the range are combination systems with individual tags, transparent sleeves, shrink-fit sleeves and markers, which can be fixed with cable ties.

General ordering data

Type	CLI R 1-3 GE/SW 9
Order No.	0572901530
Version	Conductor markers, Mounting mandrel, 3 x 4.2 mm, PVC, soft, without Cadmium, Colour: Yellow
GTIN (EAN)	4008190112967
Qty.	10 pc(s).

Conductor markers CLI R 1-3 GE/SW 9

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	3 mm	Width	4.2 mm
Height	5 mm	Depth	5 mm
Net weight	2.4 g		

General data

Colour	Yellow	Colour of printing	Black
Material	PVC, soft, without Cadmium	Material colour according to resistance code	4
Number per mandrel	25	Operating temperature range, max.	80 °C
Operating temperature range, min.	30 °C	Orientation of print	horizontal
Printed characters	Numbers	Printing	9
Printing method	Laser print	Type of printing	Standard
UL 94 flammability rating	V-0		

Conductor and cable markers

Conductor O.D., max.	5 mm	Conductor O.D., min.	3 mm
Conductor cross-section, max.	4 mm ²	Conductor cross-section, min.	1.5 mm ²
Halogen	Yes		

Classifications

ETIM 3.0	EC001530	UNSPSC	44-12-17-08
eClass 5.1	27-14-91-03	eClass 6.2	27-14-91-29
eClass 7.1	27-14-91-29		

Approvals

Approvals	
ROHS	Conform