

H1,5/16 R**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

General ordering data

Type	H1,5/16 R
Order No.	0635100000
Version	Wire end ferrule, 1.5 mm ² , 10 mm, Colour code: Weidmüller, Red (RAL 3020)
GTIN (EAN)	4008190141745
Qty.	500 pc(s).

H1,5/16 R**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technische Daten**Dimensions and weights**

Length	16 mm	Net weight	0.129 g
--------	-------	------------	---------

Product data

Conductor cross-section	1.5 mm ²	Wire connection cross section AWG, max.	AWG 16
Contact surface length (L2)	10 mm	Contact surface diameter (D1)	1.7 mm
Collar diameter (D2)	3.5 mm	Metal sleeve thickness (S1)	0.15 mm
Plastic collar thickness (S2)	0.25 mm		

Classifications

ETIM 3.0	EC000005	UNSPSC	31-16-31-02
eClass 5.1	27-40-02-01	eClass 6.2	27-40-02-01
eClass 7.1	27-40-02-01		

Approvals

Approvals



ROHS

Conform