

H0,5/14 OR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- supplied loose in polybag
- Weidmüller colour code
- DIN colour code

General ordering data

Type	H0,5/14 OR
Order No.	069070000
Version	Wire end ferrule, 0.5 mm ² , 8 mm, Colour code: Weidmüller, Orange (RAL 2000)
GTIN (EAN)	4008190015770
Qty.	500 pc(s).

H0,5/14 OR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	14 mm	Net weight	0.07 g
--------	-------	------------	--------

Product data

Conductor cross-section	0.5 mm ²	Wire connection cross section AWG, max.	AWG 20
Contact surface length (L2)	8 mm	Contact surface diameter (D1)	1 mm
Collar diameter (D2)	2.6 mm	Metal sleeve thickness (S1)	0.15 mm
Plastic collar thickness (S2)	0.25 mm		

Classifications

ETIM 3.0	EC000005	UNSPSC	31-16-31-02
eClass 5.1	27-40-02-01	eClass 6.2	27-40-02-01
eClass 7.1	27-40-02-01		

Approvals

Approvals



ROHS Conform