

VGM12-SS 68 KB 3-6.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



This cable gland series is made from stainless steel and is well suited for industrial applications requiring IP68 protection. Its excellent resistance against seawater and impacts make it ideal for use in harsh conditions.

General ordering data

Type	VGM12-SS 68 KB 3-6.5
Order No.	1009840000
Version	cable glands, Stainless steel 1.4305 (303), External thread: M 12
GTIN (EAN)	4032248714667
Qty.	50 pc(s).

VGM12-SS 68 KB 3-6.5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	28 mm	Net weight	11 g
--------	-------	------------	------

General information

AF size 1	14 mm	AF size 2	14 mm
Cable gland	metric	Clamp insert	Polyamide 6
Clamping range, max.	6.5 mm	Clamping range, min.	3 mm
External thread	M 12	Length of thread	6 mm
Material	Stainless steel 1.4305 (303)	O-Ring	NBR
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.5	Seal insert	CR
Torque for cap nut, max.	7 Nm	Torque for cap nut, min.	5 Nm
Torque for connecting adapter, max.	8 Nm	Torque for connecting adapter, min.	10 Nm

Classifications

eClass 6.2	27-18-92-34	eClass 7.1	27-18-92-34
------------	-------------	------------	-------------

Product information

Descriptive text ordering data	1.4404 (316L) on request
--------------------------------	--------------------------

Approvals

Approvals



ROHS	Conform
------	---------