

**Bolt-type screw terminals
WQL 5 WF10**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Klippon® Connect with stud Technology**

Our stud terminals are an established, robust connection alternative for particularly harsh environments. The extensive accessories and quality workmanship ensure high productivity in planning and installation – and sustainable safety in operation..

General ordering data

Type	WQL 5 WF10
Order No.	1016870000
Version	Bolt-type screw terminals, Cross-connector, No. of poles: 5
GTIN (EAN)	4032248726530
Qty.	5 pc(s).

Bolt-type screw terminals

WQL 5 WF10

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	25 mm	Width (inches)	0.984 inch
Height	163.2 mm	Height (inches)	6.425 inch
Depth	4 mm	Depth (inches)	0.157 inch
Net weight	127.8 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C		

Material data

Material	Copper - zinc	Colour	grey
----------	---------------	--------	------

Additional technical data

Installation advice	Direct mounting	Type of fixing	when screwed in
---------------------	-----------------	----------------	-----------------

Dimensions

Pitch in mm (P)	33.8 mm	TS 35 offset	36 mm
-----------------	---------	--------------	-------

Rating data

Rated current	265 A
---------------	-------

Classifications

ETIM 3.0	EC000897	ETIM 4.0	EC000897
ETIM 5.0	EC000897	ETIM 6.0	EC000489
UNSPSC	30-21-18-01	eClass 6.2	27-14-92-14
eClass 7.1	27-14-92-14	eClass 8.1	27-14-11-40
eClass 9.0	27-14-11-40	eClass 9.1	27-14-11-40

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	STEP
------------------	----------------------