

Industrial Ethernet IE-BI-USB-A

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



UNDEFINED TEXT

General ordering data

Type	IE-BI-USB-A
Order No.	1019570000
Version	USB insert, Flange insert, type A
GTIN (EAN)	4032248731602
Qty.	10 pc(s).

Industrial Ethernet IE-BI-USB-A

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight	15.6 g
------------	--------

Temperatures

Humidity	0...93 % rel. humidity	Operating temperature	-40 °C...+70 °C
Storage temperature		Installation temperature	

Technical data

Contact resistance	≤ 30 mΩ	Insulation resistance	≥ 1000 MΩ
--------------------	---------	-----------------------	-----------

General data

Product type	USB insert
--------------	------------

General Info

Colour	Black	Connection 1	USB A
Connection 2	USB A	Description of article	Flange insert, type A
Housing main material	PC UL 94 V0	Humidity	0...93 % rel. humidity
Protection degree	IP 67 with housing	Shielding	360° all-round enclosure

Electrical properties

Contact resistance	≤ 30 mΩ	Current-carrying capacity at 50 °C	1 A
Dielectric strength, contact shield	≥ 500 V DC	Insulation resistance	≥ 1000 MΩ

Standards

Connector standard	IEC 61076-3-107
--------------------	-----------------

Classifications

ETIM 3.0	EC000674	eClass 5.1	27-25-05-04
eClass 6.2	27-25-05-04	eClass 7.1	27-25-05-04

Approvals

Approvals



ROHS	Conform
------	---------

Industrial Ethernet IE-BI-USB-A

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Zeichnungen

Dimensioned drawing

