

W-Series, Accessories
WTW EN**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

The versatile and extensive range of products - from 0.05 mm² to 300 mm² - means that you have diverse options for your applications at your disposal.
Hardened steel for mechanical strength and high-quality tinned copper for optimum conductivity. All materials comply with RoHS requirements and have been tested to current environment guidelines.

General ordering data

Type	WTW EN
Order No.	1058800000
Version	W-Series, Accessories, Partition plate
GTIN (EAN)	4008190140175
Qty.	20 pc(s).

W-Series, Accessories WTW EN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	86 mm	Width	3 mm
Height	62 mm	Height of lowest version	62 mm
Net weight	13.735 g		

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Additional technical data

Installation advice	Feed-through (bushing)	Version	Intermediate plate
---------------------	------------------------	---------	--------------------

Dimensions

TS 35 offset	43 mm
--------------	-------

Material data

Material	Wemid	Colour	Dark Beige
UL 94 flammability rating	V-0		


System specifications

Product family	W-Series, Accessories
----------------	-----------------------

Classifications

ETIM 3.0	EC000886	UNSPSC	30-21-18-27
eClass 5.1	27-14-11-33	eClass 6.2	27-14-11-33
eClass 7.1	27-14-11-33		

Approvals

Approvals	
ROHS	Conform