

ClipCard
CC 15/60 O4MM MC NE SI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Similar to illustration



ClipCard O4mm MC are device markers in MultiCard format. These special versions can be easily fixed using screws or rivets through the 4.2 mm holes drilled on both sides.

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	CC 15/60 O4MM MC NE SI
Order No.	1059990000
Version	ClipCard, Device markers, 15 x 60 mm, With hole, silver
GTIN (EAN)	4032248807901
Qty.	40 pc(s).
Alternative product	1304060000
compatible printer	1324380000

ClipCard CC 15/60 04MM MC NE SI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	60 mm	Width (inches)	2.362 inch
Height	15 mm	Height (inches)	0.591 inch
Depth	1.2 mm	Depth (inches)	0.047 inch
Net weight	3 g		

General data

Application/manufacture	With hole	Colour	silver
Halogen	No	Material	Polyamide 66
Operating temperature range	-40...100 °C	Recommended industries	Machinery
UL 94 flammability rating	V-2	Width	60 mm

Device markers

Drill-hole diameter	4.2 mm	Humidity	≤ 60 %
---------------------	--------	----------	--------

Classifications

ETIM 3.0	EC001288	ETIM 4.0	EC001288
ETIM 5.0	EC001288	ETIM 6.0	EC001288
UNSPSC	30-21-18-01	eClass 5.1	27-14-91-29
eClass 6.2	27-14-91-29	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-03	eClass 9.0	27-40-06-29
eClass 9.1	27-40-06-29		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP
Software	M-Print PRO configuration file

ClipCard CC 15/60 04MM MC NE SI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Drawings

