

## Conductor markers SFC 2.5/12 MC NE BL

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



The SlimFix Clip combines two advantages: its unique closure mechanism offers the reliability of a closed marker with the ease of installation of an open marker. The clip mechanism allows quick and convenient installation of the marker even after the conductor has been installed. SlimFix Clips are suitable for conductors and cables with an outside diameter of up to 5 mm. The large marking surface - up to 30 mm - enables long character strings. The material is halogen-free and complies with flammability rating V2.

- Halogen-free material
- Flammability rating V2
- Fast installation without tools
- Markers in proven MultiCard format
- Available in the lengths of 12 mm, 21 mm and 30 mm

### General ordering data

|            |                                                                       |
|------------|-----------------------------------------------------------------------|
| Type       | SFC 2.5/12 MC NE BL                                                   |
| Order No.  | <a href="#">1062030000</a>                                            |
| Version    | Conductor markers, MultiCard, 12 x 9.3 mm, Polyamide 66, Colour: Blue |
| GTIN (EAN) | 4032248811762                                                         |
| Qty.       | 120 pc(s).                                                            |

## Conductor markers SFC 2.5/12 MC NE BL

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Dimensions and weights

|        |        |            |         |
|--------|--------|------------|---------|
| Length | 12 mm  | Width      | 9.3 mm  |
| Height | 9.1 mm | Net weight | 0.867 g |

### General data

|                                              |           |                                   |              |
|----------------------------------------------|-----------|-----------------------------------|--------------|
| Colour                                       | Blue      | Material                          | Polyamide 66 |
| Material colour according to resistance code | 6         | Operating temperature range, max. | 100 °C       |
| Operating temperature range, min.            | -40 °C    | Recommended industries            | Machinery    |
| Size of labelling field                      | 12x5.8 mm | Type of printing                  | blank        |
| UL 94 flammability rating                    | V-2       |                                   |              |

### Conductor and cable markers

|                               |                    |                               |                   |
|-------------------------------|--------------------|-------------------------------|-------------------|
| Conductor O.D., max.          | 6 mm               | Conductor O.D., min.          | 4 mm              |
| Conductor cross-section, max. | 10 mm <sup>2</sup> | Conductor cross-section, min. | 4 mm <sup>2</sup> |
| Halogen                       | No                 |                               |                   |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001530    | UNSPSC     | 39-12-14-00 |
| eClass 5.1 | 27-14-91-03 | eClass 6.2 | 27-14-91-29 |
| eClass 7.1 | 27-14-91-29 |            |             |

### Approvals

|           |         |
|-----------|---------|
| Approvals |         |
| ROHS      | Conform |

### Downloads

|                                 |                                       |
|---------------------------------|---------------------------------------|
| M-Print® PRO configuration file | <a href="#">mc_sfc_2-5_12_mcf.zip</a> |
|---------------------------------|---------------------------------------|