

**Industrial Ethernet
IE-BSC-V14M-LCD-SM-C**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



PushPull plug-in connector set according to IEC
61076-3-117 ver.14 (PROFINET), metal incl. LC insert

General ordering data

Type	IE-BSC-V14M-LCD-SM-C
Order No.	1062620000
Version	Flange FO, IP 67, Variant 14 central cable gland, LC Duplex coupling, Singlemode
GTIN (EAN)	4032248813339
Qty.	10 pc(s).

Industrial Ethernet IE-BSC-V14M-LCD-SM-C

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 52.51 g

Temperatures

Operating temperature -40 °C...+70 °C Storage temperature
 Installation temperature

General data

Colour	Miscellaneous	Connection 1	LC Duplex
Connection 2	LC Duplex	Description of article	Variant 14 central cable gland, LC Duplex coupling
Fibre type	Singlemode	Housing main material	Zinc diecast
Insertion loss	≤ 0.5 dB	Plugging cycles	500
Protection degree	IP 67	Return loss (attenuation)	≥ 40 dB
Seal material	NBR		

Standards

Connector standard IEC 61076-3-117 Var. 14,
 IEC 61754-20

Classifications

ETIM 3.0	EC001121	eClass 5.1	27-26-12-03
eClass 6.2	27-25-05-04	eClass 7.1	27-25-05-04

Approvals

Approvals



ROHS Conform

Industrial Ethernet
IE-BSC-V14M-LCD-SM-C

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

Installation cut-out

