

**Bolt-type screw terminals
WAH 185/300 BL**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Klippon® Connect with stud Technology**

Our stud terminals are an established, robust connection alternative for particularly harsh environments. The extensive accessories and quality workmanship ensure high productivity in planning and installation – and sustainable safety in operation..

General ordering data

Type	WAH 185/300 BL
Order No.	1064780000
Version	Bolt-type screw terminals, Hood, blue, 54 mm
GTIN (EAN)	4008190103200
Qty.	10 pc(s).

Bolt-type screw terminals WAH 185/300 BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	54 mm	Width (inches)	2.126 inch
Height	139 mm	Height (inches)	5.472 inch
Depth	43.9 mm	Depth (inches)	1.728 inch
Net weight	25.2 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

Material data

Material	Polyamide 66	Colour	blue
UL 94 flammability rating	V-2		

Additional technical data

Explosion-tested version	No	Type of fixing	Snap-on
--------------------------	----	----------------	---------

Dimensions

Pitch in mm (P)	55 mm
-----------------	-------

Classifications

ETIM 3.0	EC000886	ETIM 4.0	EC000886
ETIM 5.0	EC000886	ETIM 6.0	EC002848
UNSPSC	30-21-18-27	eClass 5.1	27-14-11-33
eClass 6.2	27-14-11-33	eClass 7.1	27-14-11-33
eClass 8.1	27-14-11-33	eClass 9.0	27-14-11-92
eClass 9.1	27-14-11-92		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP