

**Bolt-type screw terminals, Accessories**  
**WQL 3 WFF35****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The comprehensive range of bolt-type screw terminals offers secure connections for all power transmission applications.

Connections from 10 mm<sup>2</sup> to 300 mm<sup>2</sup> are possible. The conductors are attached to the terminals using crimped cable lugs and each connection secured by tightening the hexagonal nut.

Bolt-type screw terminals with threads from M5 to M16 can be used depending on the conductor cross-section. A low voltage drop and the use of a self-extinguishing material with a V-0 (UL 94) flammability rating guarantee maximum safety.

All bolt-type screw terminals have been tested according to international railway standards (EN 50343, EN 50155, NF F61-017, NF16-101; Ria 20) and comply with the requirements of those standards.

**General ordering data**

|            |                                                                          |
|------------|--------------------------------------------------------------------------|
| Type       | WQL 3 WFF35                                                              |
| Order No.  | <a href="#">1065400000</a>                                               |
| Version    | Bolt-type screw terminals, Accessories, Cross-connector, No. of poles: 3 |
| GTIN (EAN) | 4008190065812                                                            |
| Qty.       | 5 pc(s).                                                                 |

## Bolt-type screw terminals, Accessories WQL 3 WFF35

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Dimensions and weights

|        |       |            |         |
|--------|-------|------------|---------|
| Length | 69 mm | Width      | 15 mm   |
| Height | 3 mm  | Net weight | 23.36 g |

### Temperatures

|                       |                     |
|-----------------------|---------------------|
| Operating temperature | Storage temperature |
|-----------------------|---------------------|

### Additional technical data

|                          |    |                     |                 |
|--------------------------|----|---------------------|-----------------|
| Explosion-tested version | No | Installation advice | Direct mounting |
|--------------------------|----|---------------------|-----------------|

### Rated data

|               |       |
|---------------|-------|
| Rated current | 125 A |
|---------------|-------|

### Material data

|          |               |        |      |
|----------|---------------|--------|------|
| Material | Copper - zinc | Colour | Grey |
|----------|---------------|--------|------|

### System specifications

|                |                                           |
|----------------|-------------------------------------------|
| Product family | Bolt-type screw terminals,<br>Accessories |
|----------------|-------------------------------------------|

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000489    | UNSPSC     | 30-21-18-01 |
| eClass 5.1 | 27-14-11-40 | eClass 6.2 | 27-14-11-40 |
| eClass 7.1 | 27-14-11-40 |            |             |

### Approvals

|           |         |
|-----------|---------|
| Approvals |         |
| ROHS      | Conform |