

W-Series, Accessories
WZAD120

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The versatile and extensive range of products - from 0.05 mm² to 300 mm² - means that you have diverse options for your applications at your disposal.
Hardened steel for mechanical strength and high-quality tinned copper for optimum conductivity. All materials comply with RoHS requirements and have been tested to current environment guidelines.

General ordering data

Type	WZAD120
Order No.	1066100000
Version	W-Series, Accessories, Additional connection
GTIN (EAN)	4008190017019
Qty.	10 pc(s).

W-Series, Accessories WZAD120

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	44.412 mm	Width	24 mm
Height	10 mm	Net weight	7.6 g

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Additional technical data

Version	Additional connection
---------	-----------------------

Material data

Material	Steel	Colour	Dark Beige
----------	-------	--------	------------

System specifications

Product family	W-Series, Accessories
----------------	-----------------------

Classifications

ETIM 3.0	EC000897	eClass 6.2	27-14-11-45
eClass 7.1	27-14-92-14		

Approvals

ROHS	Conform
------	---------