

**VSSC**  
**AP VSSC6 LB****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



End plates (AP) for the VSSC product series in light blue  
and black

**General ordering data**

|            |                            |
|------------|----------------------------|
| Type       | AP VSSC6 LB                |
| Order No.  | <a href="#">1067230000</a> |
| Version    | VSSC, End plate            |
| GTIN (EAN) | 4032248999866              |
| Qty.       | 50 pc(s).                  |

**VSSC**  
**AP VSSC6 LB**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Width      | 1.5 mm  | Width (inches)  | 0.059 inch |
| Height     | 88.5 mm | Height (inches) | 3.484 inch |
| Depth      | 81 mm   | Depth (inches)  | 3.189 inch |
| Net weight | 5.8 g   |                 |            |

**Temperatures**

|                             |                |                             |                |
|-----------------------------|----------------|-----------------------------|----------------|
| Humidity                    | 5...96 %       | Operating temperature, max. | 70 °C          |
| Operating temperature, min. | -40 °C         | Storage temperature, max.   | 80 °C          |
| Storage temperature, min.   | -40 °C         | Operating temperature       | -40 °C...70 °C |
| Storage temperature         | -40 °C...80 °C |                             |                |

**General data**

|                   |            |                           |               |
|-------------------|------------|---------------------------|---------------|
| Colour            | Light Blue | Design                    | miscellaneous |
| Protection degree | IP20       | UL 94 flammability rating | V-0           |
| Version           | End plate  |                           |               |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000886    | ETIM 6.0   | EC000490    |
| UNSPSC     | 30-21-18-11 | eClass 5.1 | 27-14-11-27 |
| eClass 6.2 | 27-14-02-01 | eClass 7.1 | 27-14-11-33 |
| eClass 8.1 | 27-14-11-33 | eClass 9.1 | 27-13-92-90 |

**Approvals**

Approvals

**GOSTEX**

ROHS Conform

**Downloads**

|                  |                              |
|------------------|------------------------------|
| Engineering Data | <a href="#">EPLAN, WSCAD</a> |
| Engineering Data | <a href="#">STEP</a>         |