

VSSC
AP VSSC4 LB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



End plates (AP) for the VSSC product series in light blue
and black

General ordering data

Type	AP VSSC4 LB
Order No.	1067240000
Version	VSSC, End plate
GTIN (EAN)	4032248999873
Qty.	50 pc(s).

VSSC
AP VSSC4 LB

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	1.5 mm	Width (inches)	0.059 inch
Height	76 mm	Height (inches)	2.992 inch
Depth	58.5 mm	Depth (inches)	2.303 inch
Net weight	4.22 g		

Temperatures

Humidity	5...96 %	Operating temperature, max.	70 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	80 °C
Storage temperature, min.	-40 °C	Operating temperature	-40 °C...70 °C
Storage temperature	-40 °C...80 °C		

General data

Colour	Light Blue	Design	miscellaneous
UL 94 flammability rating	V-0	Version	End plate

Connection data

Type of connection	Screw connection
--------------------	------------------

Classifications

ETIM 3.0	EC000886	ETIM 6.0	EC000490
UNSPSC	30-21-18-11	eClass 5.1	27-14-11-27
eClass 6.2	27-14-02-01	eClass 7.1	27-14-11-33
eClass 8.1	27-14-11-33	eClass 9.1	27-13-92-90

Approvals

Approvals

GOSTEX

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP