

**Bolt-type screw terminals, Accessories
WTW WFF120**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The comprehensive range of bolt-type screw terminals offers secure connections for all power transmission applications.

Connections from 10 mm² to 300 mm² are possible. The conductors are attached to the terminals using crimped cable lugs and each connection secured by tightening the hexagonal nut.

Bolt-type screw terminals with threads from M5 to M16 can be used depending on the conductor cross-section. A low voltage drop and the use of a self-extinguishing material with a V-0 (UL 94) flammability rating guarantee maximum safety.

All bolt-type screw terminals have been tested according to international railway standards (EN 50343, EN 50155, NF F61-017, NF16-101; Ria 20) and comply with the requirements of those standards.

General ordering data

Type	WTW WFF120
Order No.	1067300000
Version	Bolt-type screw terminals, Accessories, Partition plate, Dark Beige, 2 mm
GTIN (EAN)	4008190093037
Qty.	10 pc(s).

**Bolt-type screw terminals, Accessories
WTW WFF120**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	230 mm	Width	2 mm
Height	80 mm	Net weight	64.4 g

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

Material data

Colour	Dark Beige	UL 94 flammability rating	V-0
--------	------------	---------------------------	-----

System specifications

Product family	Bolt-type screw terminals, Accessories
----------------	-------------------------------------------

Classifications

ETIM 3.0	EC000886	UNSPSC	30-21-18-27
eClass 5.1	27-14-11-33	eClass 6.2	27-14-11-33
eClass 7.1	27-14-11-33		

Approvals

Approvals	
-----------	-------------------------------------------------------------------------------------

ROHS	Conform
------	---------