

**Industrial Ethernet
IE-PI-SCRJ-MM**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



FO SC inserts for plug-in connectors ver.1 / 4 / 14

General ordering data

Type	IE-PI-SCRJ-MM
Order No.	1067380000
Version	SC insert, Plug insert SCRJ, Multi-mode
GTIN (EAN)	4032248821129
Qty.	10 pc(s).

Industrial Ethernet IE-PI-SCRJ-MM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 24 g

Temperatures

Operating temperature -40 °C...+70 °C Storage temperature
 Installation temperature

General data

Colour		Configuration	Connector and flange insert for variant 1, 4 and 14 housings
Description of article	Miscellaneous Plug insert SCRJ, Multi-mode	Housing main material	Zinc diecast
Insertion loss	≤ 0.4 dB	Plugging cycles	1000
Protection degree	IP 67 with housing	Return loss (attenuation)	≥ 30 dB

Standards

Connector standard IEC 61754-24

Classifications

eClass 6.2 27-25-05-04 eClass 7.1 27-25-05-04

Approvals

Approvals
 ROHS Conform

Datenblatt

**Industrial Ethernet
IE-PI-SCRJ-MM**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

Dimensioned drawing

