

**Industrial Ethernet
IE-BIC-HYB-P-0,75-300**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Hybrid, 10-pole. Inserts for plug-in connectors
ver.1 /4 /5 /14

General ordering data

Type	IE-BIC-HYB-P-0,75-300
Order No.	1068970000
Version	Crimp contact, Flange, Hybrid
GTIN (EAN)	4032248823956
Qty.	300 pc(s).

Datenblatt

**Industrial Ethernet
IE-BIC-HYB-P-0,75-300**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 0.29 g

Temperatures

Operating temperature _____ Storage temperature _____
 Installation temperature _____

Electrical properties

Rated voltage 24 V

Classifications

eClass 6.2 27-25-05-04 eClass 7.1 27-25-05-04

Approvals

Approvals



**Industrial Ethernet
IE-BIC-HYB-P-0,75-300**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen**Dimensioned drawing**