

**Bolt-type screw terminals, Accessories
WAP WFF35**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The comprehensive range of bolt-type screw terminals offers secure connections for all power transmission applications.

Connections from 10 mm² to 300 mm² are possible. The conductors are attached to the terminals using crimped cable lugs and each connection secured by tightening the hexagonal nut.

Bolt-type screw terminals with threads from M5 to M16 can be used depending on the conductor cross-section. A low voltage drop and the use of a self-extinguishing material with a V-0 (UL 94) flammability rating guarantee maximum safety.

All bolt-type screw terminals have been tested according to international railway standards (EN 50343, EN 50155, NF F61-017, NF16-101; Ria 20) and comply with the requirements of those standards.

General ordering data

Type	WAP WFF35
Order No.	1069700000
Version	Bolt-type screw terminals, Accessories, cover plate, Dark Beige, 2 mm
GTIN (EAN)	4008190104023
Qty.	20 pc(s).

Bolt-type screw terminals, Accessories WAP WFF35

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	23.2 mm	Width	2 mm
Height	51 mm	Net weight	1.7 g

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

Material data

Material	Wemid	Colour	Dark Beige
UL 94 flammability rating	V-0		

System specifications

Product family	Bolt-type screw terminals, Accessories
----------------	---

Classifications

ETIM 3.0	EC000886	UNSPSC	30-21-18-27
eClass 5.1	27-14-11-33	eClass 6.2	27-14-11-33
eClass 7.1	27-14-11-33		

Approvals

ROHS	Conform
------	---------