

GH PT6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The FieldPower® housings are highly robust and meet the highest UL flammability class 5 VA.

- The "TS 35 PT6" mounting rail module and PT6 contact unit are easy to snap on.
- Hinged seals allow pre-assembled plug cables to also be used.
- The high cover versions enable the device to be installed.

For cable seals consult accessories.

General ordering data

Type	GH PT6
Order No.	1070140000
GTIN (EAN)	4032248825813
Qty.	10 pc(s).

GH PT6

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	181 mm	Width	104 mm
Height	42 mm	Net weight	222 g

Temperatures

Operating temperature	-40 °C...+55 °C	Storage temperature	-40 °C...+85 °C
-----------------------	-----------------	---------------------	-----------------

General specifications

Halogen	No	Insulating material	Polycarbonate, GF 10
Protection degree	IP 65 in enclosed state	Silicone	No
Colour	Black	UL 94 flammability rating	5VA
Cover attachment	Slotted/Phillips screws	Torque for cover screws	2 Nm
Enclosure attachment	Fixing lugs		

Classifications

ETIM 3.0	EC000214	eClass 6.2	27-14-24-09
eClass 7.1	27-14-24-09		