

Accessories
STB 21.6/IH/GN WTL6/3

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The versatile and extensive range of products - from 0.05 mm² to 300 mm² - means that you have diverse options for your applications at your disposal.
Hardened steel for mechanical strength and high-quality tinned copper for optimum conductivity. All materials comply with RoHS requirements and have been tested to current environment guidelines.

General ordering data

Type	STB 21.6/IH/GN WTL6/3
Order No.	1071020000
Version	Accessories, Socket
GTIN (EAN)	4008190259228
Qty.	50 pc(s).

Accessories STB 21.6/IH/GN WTL6/3

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Width	6.2 mm	Height of lowest version	21.6 mm
Net weight	2.33 g		

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Version	For the terminals		

Dimensions

TS 32 offset	54.5 mm	TS 35 offset	54.5 mm
--------------	---------	--------------	---------

Material data

Material	Polyamide 66	Colour	Green
UL 94 flammability rating	V-2		

System specifications

Product family	Accessories	Mounting rail	TS 32, TS 35
----------------	-------------	---------------	--------------

Classifications

ETIM 3.0	EC001134	UNSPSC	30-21-18-11
eClass 5.1	27-14-11-45	eClass 6.2	27-14-92-14
eClass 7.1	27-14-92-14		

Approvals

ROHS	Conform
------	---------