

H0.5/18 OR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- supplied loose in polybag
- Weidmüller colour code
- DIN colour code

General ordering data

Type	H0.5/18 OR
Order No.	1076980000
Version	Wire end ferrule, 0.5 mm ² , 12 mm, Colour code: Weidmüller, Orange (RAL 2000)
GTIN (EAN)	403224883463 1
Qty.	500 pc(s).

H0.5/18 OR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten**Dimensions and weights**

Length	18 mm	Net weight	0.094 g
--------	-------	------------	---------

Product data

Conductor cross-section	0.5 mm ²	Wire connection cross section AWG, max.	AWG 20
Contact surface length (L2)	12 mm	Contact surface diameter (D1)	1 mm
Collar diameter (D2)	2.6 mm	Metal sleeve thickness (S1)	0.15 mm
Plastic collar thickness (S2)	0.25 mm		

Classifications

ETIM 3.0	EC000005	eClass 5.1	27-40-02-01
eClass 6.2	21-04-91-90	eClass 7.1	27-40-02-01

Approvals

ROHS	Conform
------	---------