

**Conductor markers
SFX 30/60 MC NE GR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



SlimFix X are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

- Halogen-free material
- Flammability rating V0
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

Type	SFX 30/60 MC NE GR
Order No.	1083250000
Version	Conductor markers, MultiCard, 60 x 30 mm, Polyamide 66, Colour: Grey
GTIN (EAN)	4032248847389
Qty.	30 pc(s).

Conductor markers SFX 30/60 MC NE GR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	60 mm	Width	30 mm
Height	1.2 mm	Net weight	4.6 g

General data

Colour	Grey	Material	Polyamide 66
Material colour according to resistance code	8	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Size of labelling field	30 x 45 mm
Type of printing	blank	UL 94 flammability rating	V-2

Conductor and cable markers

Conductor O.D., max.	40 mm	Conductor O.D., min.	7 mm
Conductor cross-section, min.	16 mm ²	Halogen	No

Classifications

ETIM 3.0	EC001530	UNSPSC	39-12-14-00
eClass 6.2	27-14-91-29	eClass 7.1	27-14-91-29

Approvals

Approvals	
ROHS	Conform

Downloads

M-Print® PRO configuration file	mc_sfx_30_60_mcf.zip
---------------------------------	--------------------------------------