

**OMNIMATE Housing - series CH20M
CH20M45 S 2PSC/2PSC BK**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Superior efficiency, flexibility and design - the
"standard tailor-made fit"**

When selecting a housing design, flexibility is a key factor. Other important criteria are: scalability, customised design, innovative functionality and cost efficiency. You need a choice which offers the maximum performance with the minimum overhead.

The CH20M45 modular electronics housings come in an integrated extra-large assortment. It is suited for those electronics applications that require more space, such as compact controllers and power supplies.

The entire system is characterized by excellence: outstanding scalability and flexibility, a high security level, innovative application functionality and a variety of practical details.

- **Quicker installation** with features such as "Wire ready" the universal multi-tool screw head
- **User-friendly operations:** with clear and permanent labelling and extra marking possibilities, integrated release clip or transparent cover
- **Maximum interference immunity** with EMC-compliant construction featuring deeply overlapping module joint edges made from high-performance plastic
- **High operational reliability** with the unique Auto-Set coding system and featuring double-sided touch protection on the pin header and socket blocks

CH20M - a compact name for the most flexible system available on the market. It doesn't just stand for "Component Housing IP20 Modular". CH20M also stands for efficiency and innovation throughout design, production and use.

General ordering data

Type	CH20M45 S 2PSC/2PSC BK
Order No.	1111720000
Version	Electronics housings, OMNIMATE Housing - series CH20M Black, Side element, Width: 45 mm
GTIN (EAN)	4032248890132
Qty.	6 pc(s).

OMNIMATE Housing - series CH20M CH20M45 S 2PSC/2PSC BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	105.49 mm	Width	45 mm
Height	22.83 mm	Net weight	13.2 g

System characteristics

Version	Side element	Number of connections	16
No. of connection levels	2	Number of PCBs per module	2
Contact to terminal rail	No	Encapsulation option	No

Material data

UL 94 flammability rating	V-0	Insulating material	PA 66 GF 30
Colour	Black		

Classifications

eClass 6.2	27-18-09-90	eClass 7.1	27-18-27-02
------------	-------------	------------	-------------

Approvals

Approvals	
ROHS	Conform

OMNIMATE Housing - series CH20M CH20M45 S 2PSC/2PSC BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

