OMNIMATE Signal - series RSV
BVF 7.62HP SH180 4-6 KIT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



OMNIMATE Power BV / SV 7.62HP – the 28 kVA performance class
Tailor-made solutions for high performers
More power reserves for higher load bearing capacity: The OMNIMATE Power BV / SV 7.62HP is the middle-class of the power connector systems. It has a large clamping capacity, high overload resistance and the largest range of variants and accessories to choose from: the high performer of the HP range. HP means High Performance – this performance covers a great deal: the full rated current up to 50°C without derating, unlimited 600-V approval according to UL, and the additional finger safety for 400 V-TN systems (+ 3.0 mm) in compliance with the application directive IEC 61800-5-1.

General ordering data

Type	BVF 7.62HP SH180 4-6 KIT
Order No.	1118470000
Version	PCB plug-in connector, Accessories
GTIN (EAN)	4032248899456
Qty.	25 pc(s).
Product data	

OMNIMATE Signal - series RSV
BVF 7.62HP SH180 4-6 KIT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight	32.105 g

Classifications

eClass 6.2	27-26-92-01	eClass 7.1	27-44-92-02

Notes

Notes

Approvals

Approvals