

BG GHDE 10P PT6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The FieldPower® housings are highly robust and meet the highest UL flammability class 5 VA.

- The "TS 35 PT6" mounting rail module and PT6 contact unit are easy to snap on.
- Hinged seals allow pre-assembled plug cables to also be used.
- The high cover versions enable the device to be installed.

For cable seals consult accessories.

General ordering data

| | |
|------------|--|
| Type | BG GHDE 10P PT6 |
| Order No. | 1122200000 |
| Version | Enclosures, IP 65 with corresponding housing, Polycarbonate, GF 10 |
| GTIN (EAN) | 4032248903207 |
| Qty. | 10 pc(s). |

BG GHDE 10P PT6

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

| | |
|------------|---------|
| Net weight | 235.1 g |
|------------|---------|

Temperatures

| | | | |
|-----------------------|-----------------|---------------------|-----------------|
| Operating temperature | -40 °C...+55 °C | Storage temperature | -40 °C...+85 °C |
|-----------------------|-----------------|---------------------|-----------------|

General specifications

| | | | |
|-------------------|----------------------------------|---------------------------|----------------------|
| Halogen | No | Insulating material | Polycarbonate, GF 10 |
| Protection degree | IP 65 with corresponding housing | Silicone | No |
| Colour | Black | UL 94 flammability rating | 5VA |
| Cover attachment | Slotted/Phillips screws | Torque for cover screws | 2 Nm |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000214 | eClass 6.2 | 27-14-24-09 |
| eClass 7.1 | 27-14-24-09 | | |