

304382, MC CRYPT AT 3600L PLATTENSPIELER-SYSTEM

Dual-moving-magnet type stereo phone

Sturdy silver body with tracking arm

Rubber washer for snug fit to tone arm

Elliptical stylus for strong tracking

Stylus cover for extended life span

Specifications :

- Suggested Stylus Force : 3.5 ± 0.5 gr
- Load Impedance : $47K\Omega$
- Load Capacitance : 100Pf
- DC Resistance : $410\Omega \pm 20\%$
- Vertical tracking angle : 24°
- Voltage Out : 2.5mV
- Channel Separation : 23db
- Balance : <3db
- FIM Distortion : 1%
- Hum Sensitivity : 0.5mV

