

EUROLITE SB-1100 19" distributor 32A



No. 30248375

- 3 U necessary for installation
- Three phase current input via power cable and plug
- Three phase current output via mounted plug secured on the rearpanel by a Residual Current Device (RCD)
- The entire distributor is secured via 30 mA Residual Current Device (RCD)
- 2 mounted CEKON sockets with 16 A on the front panel, secured via 3 x 16 A fuse blocks
- Control lamps indicate each phase
- 6 safety sockets on the housing back (2 per phase)
- With M6 earthing screw in order to ground a rigg if necessary

Technical specifications:

Power supply:	380-400 V AC, 50 Hz ~
Max. power output:	22080 W
Max. output/phase:	7360 W
Max. current/phase:	32 A
Fuses:	2x 16A 3 Ph, 3x 16A 1 Ph, FI/RCD 40A/0.03A
Height:	3 U
Dimensions (LxWxH):	482 x 295 x 132 mm
Weight:	6.9 kg