


**SwitchMark
SM 22/22 K MC NE GE**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Similar to illustration



SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet PRO, MCP Plus plotter, MCP Basic or MC-Mobilo marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

Please note that these markers are not intended for printing with the SpeedMarking laser.

General ordering data

Type	SM 22/22 K MC NE GE
Order No.	1131830000
Version	SwitchMark, Device markers, 22 x 22 mm, yellow
GTIN (EAN)	4032248912452
Qty.	80 pc(s).
compatible printer	1324380000

SwitchMark SM 22/22 K MC NE GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	22 mm	Width (inches)	0.866 inch
Height	22 mm	Height (inches)	0.866 inch
Depth	1 mm	Depth (inches)	0.039 inch
Net weight	1.613 g		

General data

Adhesive	Double-sided adhesive tape	Colour	yellow
Halogen	No	Material	Polyamide 66
Material colour according to resistance code	4	Operating temperature range	-40...100 °C
UL 94 flammability rating	V-2	Version	Self-adhesive
Width	22 mm		

Classifications

ETIM 3.0	EC001288	ETIM 4.0	EC001288
ETIM 5.0	EC001288	ETIM 6.0	EC001288
UNSPSC	30-21-18-01	eClass 5.1	27-14-91-29
eClass 6.2	27-37-12-25	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-03	eClass 9.0	27-40-06-29
eClass 9.1	27-40-06-29		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP
Software	M-Print PRO configuration file

SwitchMark SM 22/22 K MC NE GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

