

**Device markers  
CC 15/60 K MC NE GE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



ClipCard device markers in MultiCard format are used for labelling electrical installations and switchgear systems, and offer an interesting alternative to engraving. Thanks to the proven MultiCard format, labelling is possible with PrintJet PRO, the MCP Plus plotter, MCP Basis and MC-Mobilo.

- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- Universal fixing
- Carrier (screwable or with cable ties)
- Tag rail (self-adhesive or screw fixing)
- Or self-adhesive tags

**General ordering data**

|            |                                                                     |
|------------|---------------------------------------------------------------------|
| Type       | CC 15/60 K MC NE GE                                                 |
| Order No.  | <a href="#">1131890000</a>                                          |
| Version    | Device markers, MultiCard, 15 x 60 mm, Polyamide 66, Colour: Yellow |
| GTIN (EAN) | 4032248915026                                                       |
| Qty.       | 40 pc(s).                                                           |

## Device markers CC 15/60 K MC NE GE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Dimensions and weights

|        |        |            |         |
|--------|--------|------------|---------|
| Length | 15 mm  | Width      | 60 mm   |
| Height | 1.2 mm | Net weight | 3.375 g |

### General data

|                                              |                            |                                   |                                  |
|----------------------------------------------|----------------------------|-----------------------------------|----------------------------------|
| Adhesive                                     | Double-sided adhesive tape | Application/manufacturer          | Holder CC-H 15/60, Self-adhesive |
| Colour                                       | Yellow                     | Material                          | Polyamide 66                     |
| Material colour according to resistance code | 4                          | Operating temperature range, max. | 60 °C                            |
| Operating temperature range, min.            | -40 °C                     | Recommended industries            | Machinery                        |
| UL 94 flammability rating                    | V-2                        |                                   |                                  |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001288    | UNSPSC     | 30-21-18-01 |
| eClass 5.1 | 27-14-91-29 | eClass 6.2 | 27-14-91-29 |
| eClass 7.1 | 27-14-91-29 |            |             |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                                 |                                     |
|---------------------------------|-------------------------------------|
| M-Print® PRO configuration file | <a href="#">mc_cc_15_60_mcf.zip</a> |
|---------------------------------|-------------------------------------|