RIDERSERIES
SCM-I QV S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Cross-connector for bridging connections in the RIDERSERIES RCM

General ordering data

Type	SCM-I QV S
Order No.	1132080000
Version	RIDERSERIES, Cross-connector, No. of contacts: 6, Continuous current: 12 A
GTIN (EAN)	4032248912193
Qty.	10 pc(s).

RIDERSERIES
SCM-I QV S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Width	23 mm	Net weight	6.7 g

Temperatures

Operating temperature	-45 °C...+70 °C	Storage temperature	-40 °C...+85 °C

Input

Coil resistance		Pull-inrop-out current, typ.	
Pull-inrop-out typ.			

Output

Continuous current	12 A

Contact data

No. of contacts	6

Insulation coordination

Protection degree	IP 20

Classifications

eClass 6.2	27-14-11-40	eClass 7.1	27-37-16-03

Approvals

Approvals	ME25
ROHS	Conform